

QUADRA™ 5

X-ray Inspection System

The Flexible X-ray Inspection Solution

Quadra™ 5 offers excellent functionality and sub micron image quality. Images are acquired at 3MP resolution and displayed in real time on a High Definition 24" monitor.

Quadra 5 shares many of the same accessories as Quadra™ 7, including the μ CT acquisition stage, heated sample stage for solder reflow simulation, X-ray dose filtering and thin sample trays.

See the Finest Details


Over 30 advanced image enhancement filters create clear, easy to interpret images from the Aspire FP™ detector.

Simplicity as Standard


Gensys™ proprietary control and measurement software features an intuitive point and click interface so even occasional users can acquire high quality X-ray images quickly, and with minimal training.

Maintenance Free


The QuadraNT™ X-ray source uses proprietary filament free technology, so regular preventative maintenance visits are not required, reducing your downtime and running costs.



4-way split screen view with filters and void calculations for easier identification.



Automatic BGA void calculations with exportable reports.




Head-in-Pillow effortlessly identified using X-Plane®.

Seeing is Believing™
QUADRA

Specifications at a Glance

Options	
X-Plane®	View sample slices without additional CT hardware
Visualization for X-Plane	Create 3D models from X-Plane data
µCT	Create high resolution 3D models with the µCT sample stage
Heated Stage	Simulate reflow oven conditions, view solder processes in real time
HDR	High Dynamic Range Imaging enables you to see defects in very bright and very dark areas of the same image
Joysticks	For joystick navigation and zoom
Barcode Reader	Track samples easily
Second Monitor	See board overview and reference images more clearly
Filtering Tray	Reduce sample X-ray dose
Thin Sample Tray	Acquire clearer images of thin samples at low kV
Reel Handler	Inspect components packaged on tape and reel



Pad voiding in a QFN.

QuadraNT™ X-ray Tube	
Type	Filament free transmissive
Feature Recognition	0.35 µm (0.95 µm above 10 W)
Target Power	20 W
Voltage	30-160 kV

Aspire FP™ Detector	
Resolution	3 MP
Frame Rate	25 fps
Pixel Pitch	50 µm
Digital Imaging Processing	16-bit

Inspection	
Oblique Angle View	2 × 70° - No sample rotation required
Anti Vibration	AXiS - Active X-ray Image Stabilization
Display Resolution	94 PPI
Inspection Area	510 x 445 mm (20 x 17.5")
Geometric Magnification	2,500x
Total Magnification	45,000x
Sample Weight (standard tray)	5 kg (11 lbs)
Display	Single 24" WUXGA 1920 x 1200 on Fully Flexible Arm Mount

System	
Footprint	1570 W x 1500 D x 1900 H mm
System Weight	1950 kg (4300 lbs)
Power Supply	Single phase 200-230 VAC, 50/60 Hz, 16A
Typical Power Consumption	1kW
Air Supply	5-8 bar clean, dry for anti-vibration
Operation Temperature	10-30°C
Humidity	<85 % (non-condensing)
Operation	Mouse point and click
OS	Windows 10 64-bit
X-ray Safety	<1 µSv/hr Meets all international standards

Nordson Test & Inspection Europe, SEA, Africa
ti-sales-eu@nordson.com

Nordson Test & Inspection Americas
ti-sales-us@nordson.com

Nordson Test & Inspection China
ti-sales-cn@nordson.com

Nordson Test & Inspection Japan
ti-sales-jp@nordson.com

Nordson Test & Inspection Singapore
ti-sales-eu@nordson.com

Nordson Test & Inspection Taiwan
ti-sales-tw@nordson.com

Nordson Test & Inspection Korea
ti-sales-korea@nordson.com

